

Setting the Standard
Since 1985

- Clinical Use
Areas:
- >> ED
 - >> PACU
 - >> ICU
 - >> Step-down/
Telemetry
 - >> Procedure Areas

Available in Continuous or Intermittent

The 3800 Series Adult Suction Regulators can outfit every area of the modern acute care hospital. The factory 12-year warranty, coupled with the lowest demonstrated cost of ownership in the industry gives administrators the confidence that they are buying capital equipment that will last the service lifetime of new construction or renovation.



ADULT SUCTION REGULATORS

The 3800 series is covered by the only validated reprocessing means in the industry, giving clinicians the peace of mind that this equipment need not be thrown away if inadvertently contaminated, and affords compromised patients a higher level of safety. Setting Memory™ allows clinicians to easily and accurately apply suction without complex setup procedures.

- Features:**
- Longest warranty in the industry – 12-year factory warranty
 - Patented Self-Clearing™ technology ensures years of trouble-free operation
 - Sterilizable – VSS270™



Boehringer 3800 Series Suction Regulators Compared to Competitors

Feature	Competitors	Boehringer
Regulated Range	Can apply full line suction without any indication by continually turning adjustment knob.	Factory limited to 200mmHg in accordance with AACN and AARC guidance.
Full Line Safety	Can inadvertently apply full line suction if control knob is turned to this setting.	Integral factory safety necessitates clinical input before applying full line suction.
Serviceable	Upon fluid intrusion, repair parts alone can equal 40% of the purchase price of the unit.	Can be cleaned and is serviceable with no tools required.
Setting Memory™	Requires clinicians occlude to set, or the regulator has a complex self-occluding system to ensure reliable output pressures.	Can be set in either intermitting or continuous modes, with or without the catheter open.
Contamination	Warranty voided. Mfg. recommends disposal of unit.	Can be easily reprocessed for subsequent patient use.
Durability	Plastic construction; susceptible to damage if dropped, being hit by a bed, or aggressive cleaning agent.	All metal construction, even the fittings are warranted when factory installed. Drop tolerant.

Model Overview

Model	Intermit	Line	Regulated Range	Ports	Dimensions	Weight	Modes
3800	No	Yes	20-200 mmHg	1/8 NPTF	5 3/4 x 2 1/2 x 4	22 oz	OFF – REG – LINE
3804	Yes	No	20-200 mmHg	1/8 NPTF	5 3/4 x 4 1/8 x 4	26 oz	OFF – INTERMIT – CONT